



- 1 Type**
- DK** With triangular spindle
 - VK7** With square spindle
 - VK8** With square spindle
 - SCH** With slot
 - VDE** With double bit

2

Latch arm distance A

6	10	14	18	20	22	24	26	28	30	34	38	40	50
---	----	----	----	----	----	----	----	----	----	----	----	----	----

Specification

3

- Lock housing
Stainless steel AISI 303 **NI**
- Latch arm
Stainless steel AISI 304
- Other parts
Stainless steel AISI 304
- Protection class IP 65
- IP Protection Classes → Page 2153
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Socket Keys GN 119.2 → Page 1266
- Protective Caps GN 120 → Page 1268
- Opening Handles GN 120.1 → Page 1269
- Protective Guide Plates GN 120.2
→ Page 1270
- Internal Cabinet Handles GN 120.3
→ Page XYZ
- Sheet metal punches GN 123 → Page XYZ

On request

- Other operations

Information

Latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

Latches GN 115 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.
- Latches GN 115 (Stainless Steel, Lockable) → Page 1208
- Latches GN 115 (Steel, Zinc Plated, Operation with Socket Key)
→ Page 1202

How to order

GN 115-DK-18-NI

1	Type
2	Latch arm distance A
3	Material

