



1		2		3		d ₁	d ₂	d ₃	d ₄	m ₁		m ₂	m ₄	m ₅	s
l ₁	On one side elongated	On both sides elongated	l ₂							On one side elongated	On both sides elongated				
45	60	30	3	3,2	4	6,4	33	48	18	9	24	1,5			
60	80	40	4	4,2	5	8,3	45	65	25	12,5	32,5	2			
75	100	50	6	5,2	5	8,3	55	80	30	15	40	2			
90	120	60	6	5,2	5	8,3	66	96	36	18	48	2			

1	
Specification	
Hinge leafs	
• Steel	ST
• Zinc plated, blue passivated	
• Only type B / C	
• Stainless steel AISI 304	NI
- Plain finish	
• All types	
- Powder coated	• NISW
• Black, RAL 9005, textured finish	
• Only type B	
• Stainless steel AISI 316	A4
• Only type B / C	
Pin	
Stainless Steel	
• AISI 304 for ST / NI / NISW	
• AISI 316 for A4	
• Riveted	

RoHS

How to order

1

2

3

4

GN 136-ST-60-40-B

1	Material
2	l ₁
3	l ₂
4	Type