




 **Inox**
Stainless
Steel

l ₂	s				b ₁	b ₂	d	l ₁	m ₁	m ₂	Suitable for hinges with hole spacing m ₂					
											GN 235	GN 337	GN 337.1	GN 437	GN 7231	GN 7233
30	1	1,5	3	5	10,8	6	4	30	18	18	-					
40	1	1,5	3	5	14,5	7,5	5	40	25	25	x					
50	1	1,5	3	5	18	10	6	50	30	30	x					
60	1	1,5	3	5	21,5	12,5	8	60	36	36	x					

Specification

- Stainless steel AISI 304 **NI**
Matte finish, ground **MT**
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Tolerances of chamfers, different sheet metal thicknesses or the use of seals could mean that the mounting surfaces of the hinges on the frame and door do not have the desired separating distance.

Spacer plates GN 2370 are designed as accessories for multiple families of hinges, and their dimensions allow them to be used as shims either individually or in combination to achieve the desired position or height compensation.

The table includes a number of potential compensation heights which can be accomplished by shimming with one or two spacer plates.

Height compensation	Plate thickness s	Height compensation	Plate thickness s
1	1	4,5	3 + 1,5
1,5	1,5	5	5
2	1 + 1	6	3 + 3
2,5	1 + 1,5	6,5	5 + 1,5
3	3	8	5 + 3
4	3 + 1	10	5 + 5

How to order	1 Material
	2 l ₂
	3 s
	4 Finish

1

2

3

4

GN 2370-NI-40-5-MT