



- 3 Type**
- D** With internal thread
 - E** With threaded stud

1 d ₁	2 d ₂ Type D	2 d ₃ Type E	d ₄	h	Length l	t min.
16	M 5	M 6	10	18	10	7
20	M 6	M 8	12	24	12	9
25	M 6	M 8	14	29	14	9
32	M 8	M 10	18	37	16	12
36	M 10	M 12	20	42	18	15

Specification

GN 75
Steel

- Fine turned
- Blackend
- Zinc plated, blue passivated

GN 75.5
Stainless steel AISI 304

- Matte shot-blasted finish
- Highly polished

RoHS

On request

- Version in stainless steel (A4 quality)

4

—
ZB

MT
PL

Mushroom shaped knobs GN 75 / GN 75.5 have a compact and timeless design. Their non-scooping geometry combats dirt build-up and makes cleaning easier.

Mushroom shaped knobs GN 75 in steel are mainly used in mechanical engineering. Mushroom shaped knobs GN 75.5 can be used in aggressive environments thanks to the stainless steel used.

see also...

GN 676.1 Knobs (Steel, Blackened)	Page QVX
GN 676.2 Knobs (Steel, Zinc Plated)	QVX
GN 676.5 Stainless Steel Knobs (Edelstahl)	QVX

Technical Information

Stainless Steel Characteristics QVX

How to order (Steel, blackened)

1 **2** **3**

GN 75-25-M6-D

1	d ₁
2	d ₂ (d ₃)
3	Type

Bestellbeispiel (Steel, zinc plated)

1 **2** **3** **4**

GN 75-32-M10-E-ZB

1	d ₁
2	d ₃ (d ₂)
3	Type
4	Finish

How to order (Stainless steel)

1 **2** **3** **4**

GN 75.5-25-M8-E-MT

1	d ₁
2	d ₃ (d ₂)
3	Type
4	Finish