



3 Type  
D With internal thread  
E With threaded stud

d <sub>1</sub>	d <sub>2</sub> Type D	d <sub>3</sub> Type E	d <sub>4</sub>	d <sub>5</sub>	h	Length l	t min.
20	M 5	M 5	14	14,8	24	10	7
25	M 6	M 6	16	16,8	29	12	9
32	M 8	M 8	18	18,8	37	14	12

Specification

**Knob**  
Stainless steel AISI 316L  
• Matte finish (Ra < 0.8 µm)  
• Polished finish (Ra < 0.8 µm)

MT  
PL

Sealing ring

- H-NBR
- EPDM
- FDA compliant material
- Blue
- Hardness 85±5 Shore A

H  
E

RoHS

On request

- with FKM sealing ring (Fluorine rubber)

F

Mushroom shaped knobs GN 75.6 are intended for use in hygienic areas. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning. They have a compact and timeless design.

Technical Information

	Page
Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 7600 Sealing Rings	QVX
-----------------------	-----

How to order	1 d <sub>1</sub>
	2 d <sub>2</sub> (d <sub>3</sub> )
	3 Type
	4 Finish
	5 Material (Sealing ring)

GN 75.6-25-M6-E-MT-H