



**4 Form**  
A rundstirnig

| 1               |   | 2       |    | 3  |    |    |    |    |    |    |    |    |    |    |     |     |    |     |         |                             |  |  |  |
|-----------------|---|---------|----|----|----|----|----|----|----|----|----|----|----|----|-----|-----|----|-----|---------|-----------------------------|--|--|--|
| b <sub>h9</sub> | h | Länge l |    |    |    |    |    |    |    |    |    |    |    |    |     |     |    |     |         | für<br>Wellen-Ø<br>über bis |  |  |  |
| 2               | 2 | 6       | 8  | 10 | 12 | 14 | 16 | 18 | 20 | -  | -  | -  | -  | -  | -   | -   | -  | -   | 6...8   |                             |  |  |  |
| 3               | 3 | 6       | 8  | 10 | 12 | 14 | 16 | 18 | 20 | 22 | 25 | 28 | 30 | 32 | 35  | 36  | -  | -   | 8...10  |                             |  |  |  |
| 4               | 4 | 6       | 8  | 10 | 12 | 14 | 16 | 18 | 20 | 22 | 25 | 28 | 32 | 36 | 40  | 45  | -  | -   | 10...12 |                             |  |  |  |
| 5               | 5 | 8       | 10 | 12 | 14 | 16 | 18 | 20 | 22 | 25 | 28 | 32 | 36 | 40 | 45  | 50  | -  | -   | 12...17 |                             |  |  |  |
| 6               | 6 | 12      | 14 | 16 | 18 | 20 | 22 | 25 | 28 | 32 | 36 | 40 | 45 | 50 | 56  | 63  | -  | -   | 17...22 |                             |  |  |  |
| 8               | 7 | 12      | 14 | 16 | 18 | 20 | 22 | 25 | 28 | 32 | 36 | 40 | 45 | 50 | 56  | 63  | 70 | 80  | 22...30 |                             |  |  |  |
| 10              | 8 | 16      | 18 | 20 | 22 | 25 | 28 | 32 | 36 | 40 | 45 | 50 | 56 | 63 | 70  | 80  | 90 | 100 | 30...38 |                             |  |  |  |
| 12              | 8 | 20      | 25 | 28 | 32 | 36 | 40 | 45 | 50 | 56 | 63 | 70 | 80 | 90 | 100 | 125 | -  | -   | 38...44 |                             |  |  |  |

Ausführung

Stahl C45

blank

RoHS

Auf Anfrage

• b = 14, 16, 18, 20

Passfedern DIN 6885 sind nur in Verpackungseinheiten von 50 Stück je Größe und Länge lieferbar.

Hinweise

DIN 6885 Passfedern (Edelstahl)

Seite

QVX

Technische Informationen

Passfedernuten DIN 6885-1 (hohe Nabennut)

QVX

Passfedernuten DIN 6885-2 (niedrige Nabennut)

QVX

ISO-Passungen

QVX

Bestellbeispiel

**DIN 6885-6-6-28-A**

1 b  
2 h  
3 Länge l  
4 Form