



1 Type

- SC** With key (same lock)
- SCKN** With wing knob (same lock)
- SCTN** With T-Handle (same lock)

2

Latch distance A												d		h			
6	10	14	18	20	22	24	26	28	30	34	38	40	50	Type SC	Type SCKN, SCTN	Type SC	Type SCKN, SCTN
														28	32	4	6

Specification

- Lock housing **NI**
 - Type SC
Stainless steel AISI 303
 - Type SCKN, SCTN
Stainless steel AISI 316
- Latch arm
Stainless steel AISI 304
- Key
Nickel silver with plastic hand piece
- Operating elements (Type SCKN, SCTN)
Stainless steel AISI 316
- Other parts
 - Type SC
Stainless steel AISI 304
 - Type SCKN, SCTN
Stainless steel AISI 316
- Protection class IP65 (Type SCKN, SCTN)
- IP Protection Classes → Page 1253
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessories

- Protective Caps GN 120 → Page 1268
- Opening Handles GN 120.1 → Page 1269
- Protective Guide Plates GN 120.2
→ Page 1270
- Sheet Metal Punches GN 123 → Page XYZ

On request

- Latch arm in A4
- Lock with Different Combinations

3

Information

The lockable latches GN 115 lock by a turning operation limited to 90° which moves the locking behind the door frame. The bevels of the locking ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

The latches are delivered with 2 keys and loosely enclosed latch arm. The key can be removed in both end positions. The lock is standard, so that every lock can be opened with the same key.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.
- Latches GN 115 (Stainless Steel, Operation with Socket Keys) → Page 1202
- Latches GN 115 (Stainless Steel, with Operating Elements) → Page 1200

How to order

GN 115-SC-40-NI

1	Type
2	Latch distance A
3	Material