



- 3 Type**
- E** With cover cap (threaded blind bore)
 - C** With cover cap (blind bore H9)
 - D** Without cover cap (threaded through bore)

d ₁	d ₂ Type E			d ₃ Type D			d ₄ H9 Type C		d ₅	d ₆	h ₁	h ₂	t ₁	t ₂ min.
25*	M 4	M 5	M 6	-	-	-	-	-	13	8	19	8	10	-
32	M 5	M 6	M 8	M 5	M 6	M 8	B 6	-	15	10	23	10	12	12
40	M 6	M 8	-	M 6	M 8	-	B 8	-	17	13	27	12	18	14
40	M 10	-	-	M 10	-	-	-	-	17	13	27	12	17	-
50	M 8	M 10	M 12	M 8	M 10	M 12	B 8	B 10	19	15	32	14	20	14
63	M 8	M 10	M 12	M 8	M 10	M 12	B 8	B 10	22	19	37	16	26	20
74	M 12	M 14	-	M 12	M 14	-	B 8	B 12	26	17	43,5	22	26	20
74	M 16	-	-	M 16	-	-	B 16	-	26	17	43,5	22	31	20
84	M 12	M 16	-	M 12	M 16	-	B 12	B 16	28	22	44	21	25	25
95*	M 16	-	-	-	-	-	-	-	32	19	46	21	22	-

* only available in black

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Reinforced, shock-resistant
- Temperature resistant up to 90 °C
- Black, matte finish
- Type E and D
Bushing brass
- Type C
Bushing steel
- Color of the cover cap (matte finish):

● -	-
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
● DGN	Green, RAL 6017

- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

Information

Characteristic of the star knobs GN 5337.2 is the 5 lobes. They not only give the knobs a specific style but this shape has also enabled the operator to achieve a higher torque.

see also...

- Star Knobs GN 5337.7 (Bushing Stainless Steel) → Page 562
- Star Knobs GN 5337 (Duroplast) → Page 556
- Star Knobs GN 5337.4 (Bushing Stainless Steel) → Page 564
- Softline Star Knobs GN 5337.6 → Page 566
- Star Knobs GN 5337.2 with Loss Protection GN 111.7 → Page 2084

How to order (Cover cap black)	1 d ₁
GN 5337.2-40-M8-E	2 d ₂ (d ₃ , d ₄)
	3 Type

How to order (Cover cap colored)	1 d ₁
GN 5337.2-32-M5-E-DBL	2 d ₂
	3 Type
	4 Color of the cover cap