






elesa
Original design TCC-PB / TCC-PBF

 **GERMAN DESIGN AWARD**

3 Type
OZ Without centring step (smooth)
AV With external serration

1 **2**

b	x ₁	d ₁	d ₂	Length l	m ₁	m ₂	t ₁	t ₂	s	x ₂	y ₁	y ₂
Swivel width												
40	40	8,5	6,5	54	33	20	-	8	13,5	-	75	60
40	75	8,5	6,5	54	33	37,5	30	8	13,5	60	75	60

Specification

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -20 °C to +100 °C
- Black, RAL 9005, matte finish
- Gray, RAL 7040, matt finish

● **SW**
○ **GR**

RoHS

The fixing lug of the swivel clamp connector bases GN 272.9 is available with a smooth surface or with external serration.

The flange with two or four bores serves for fastening the clamp connector.

Swivel clamp connector bases GN 272.9 can be assembled with swivel clamp connectors GN 276.9 and GN 278.9 to create swivel clamp connector joints.

see also...	Page
GN 282.9 Swivel Clamp Connector Joints	QVX
GN 276.9 Swivel Clamp Connectors	QVX
GN 278.9 Swivel Clamp Connectors	QVX
GN 272 Swivel Clamp Connector Bases (Aluminium)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

1	b
2	x ₁
3	Type
4	Color

GN 272.9-40-75-OZ-SW