



¹ b ₁	² l ₁ ±0,25	a	b ₂	d	h -1	l ₂ ≈	l ₃	l ₄ ≈	l ₅ max.
26	350	17	14	M 8	69	526	328	18	9,5
26	450	17	14	M 8	69	632	428	18	9,5

Specification ³

Arch handle

Aluminum

Powder coated

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

● SW
● SR

End pieces

Zinc die casting

Powder coated

Silver, RAL 9006, textured finish

Grub screws

Steel, property class 5.8

Zinc plated, blue passivated

Hex nuts ISO 4032-M8

Steel, zinc plated

Washers DIN 125

Steel, zinc plated

RoHS

see also...

Page

GN 565.4 Arch Handles (Aluminum, Mounting from the Back or Operator's Side) QVX

GN 428 Cabinet U-Handles (Aluminum) QVX

Technical Information

Strength Values of Screws QVX

Load Rating Information QVX

How to order

¹ ² ³
GN 665-26-450-SW

1 b₁

2 l₁

3 Finish