



1				2						
l ₁	d ₁ Thread			d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
22	M 3	M 4	M 5	8	10,5	18,5	2	16,5	3	5
30	M 4	M 5	M 6	10	13	24,5	4	22	3,5	9
45	M 4	M 5	M 6	10	13	24,5	4	22	3,5	9
63	M 6	M 8	-	13,5	17,5	31	6,5	28,5	4	11
78	M 8	M 10	-	16	21	36	8	34	4	14

Specification

• Handle

Zinc die casting

• Powder coated

Black, RAL 9005, textured finish

Orange, RAL 2004, textured finish

Red, RAL 3000, textured finish

Silver, RAL 9006, textured finish

• Bushing and retaining screw

Steel

Zinc plated, blue passivated

• RoHS

3

● SW

● OS

● RS

● SR

Information

Adjustable hand levers GN 302.2 have a straight lever, not inclined, being parallel to the clamping space.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

• Flat Adjustable Hand Levers GN 302 (Bushing Steel Blackened)

→ Page QVX

• Flat Adjustable Hand Levers GN 302.1 (Bushing Stainless Steel)

→ Page QVX

• Adjustable Hand Levers GN 300.2 (Bushing Steel Zinc Plated)

→ Page QVX

How to order	1	l ₁
GN 302.2-63-M6-SW	2	d ₁
	3	Color

2.1 Tensioning, clamping, switching with levers |

Page 1