



d <sub>1</sub>	Length l		d <sub>2</sub>	h	r	t min.
	SW / SR / BL	SMA / WSA				
20	200	200	M 8	68	22	15
20	250	250	M 8	68	22	15
20	300	300	M 8	68	22	15
20	350	-	M 8	68	22	15
28	250	250	M 10	78	32	15
28	300	300	M 10	78	32	15
28	350	-	M 10	78	32	15
28	400	400	M 10	78	32	15

Specification

Aluminum

- Powder coated, textured finish
  - Black, RAL 9005, UV-resistant
  - Silver, RAL 9006
- Powder coated, antimicrobial
  - White, RAL 9016
  - Black, RAL 9005
- Plain finish, tumbled

RoHS

AL

- SW
- SR
- WSA
- SMA
- BL

Cabinet U-handles GN 426 are manufactured from a bent aluminum profile and have excellent stability and ergonomic design. In addition to the standard surfaces, these cabinet U-handles are also available with a functional coating.

The **SMA / WSA** versions have a powder coating based on silver ions, which gives them antimicrobial properties. The principle of action has been shown to reduce the contamination of the handle surfaces within 24 hours so that fewer than 1% of bacteria and fewer than 5% of viruses ultimately survive. Standard parts with antimicrobial plastic coating are primarily used in the health care sector and in public buildings, such as airports, train stations, stadiums, etc.

see also...	Page
GN 428 Cabinet U-Handles (Aluminum)	QVX

Technical Information

Product family Sanline	QVX
Load Rating Information	QVX

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
---	-----

How to order	1 Material
	2 d <sub>1</sub>
	3 Length l
	4 Finish
GN 426-AL-28-300-SW	