




Length l	¹ d ₁ H7 Bore	² s H11 Square	d ₂	d ₃	h ₁	h~2~	h ₃	h ₄ ≈	Ø Handle GN 598
80	B 10	V 10	23	26	24	14	14	52,5	21
100	B 12	V 12	27	30	28	17	15	67,5	23
125	B 14	V 14	32	35	34	22	18	82,5	26
160	B 17	V 17	35	39	38	26	18	82,5	26

Specification

GN 471
Body
Aluminum
• Plastic coated
black, textured finish
• Contact face of hub machined
GN 471.1
Body
Zinc die casting
Plastic coated
Back, textured finish
Revolving handles GN 598
Plastic, Polyamide (PA)
• Black, matte finish
• Spindle steel
Zinc plated, blue passivated

RoHS

Cranked handles GN 471 / GN 471.1 are used for making adjustments or driving mechanisms.
The cranking movement is transmitted via the freely revolving cylindrical handle. The revolving handle can be held firmly and safely while cranking.
Cranked handles can also be ordered with cross holes GN 110.

see also...	Page
GN 570 Cranked Handles (Plastic, with Bore)	QVX
GN 570.1 Cranked Handles (Plastic, with Square)	QVX

Technical Information	
Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order (Aluminum) ¹ GN 471-80-B10	¹ Length l
	² d1(s) (s)
How to order (Zinc die casting) ¹ GN 471.1-50-V8	¹ Length l
	² d ₁ (s)