




Mounting examples



1	2						
l_1	h		d_1	$d_2^{H8/h8}$	l_2	$l_3 \pm 0,01$	t
30	25	50	M 6	9	13	17	8
40	35	70	M 8	11	17	23	12
50	45	80	M 10	13	20	30	15
60	50	85	M 10	13	20	40	15

Specification

Steel C45

Chemically nickel plated

RoHS



NC

Clamping jaws GN 872 are designed to be modified by the user into individual clamping designs, such as prisms and radii. They are also suitable for welding.

The fastening thread and centering bores are adapted to the dimensions of the clamping arms and static holders to enable quick and easy assembly. Centering guide bushings GN 870 are **not** included.

Technical Information

ISO Fundamental Tolerances

Page

QVX

Accessory

GN 870 Centering Guide Bushings

QVX

How to order

GN 872-50-80-NC

1	l_1
2	h
3	Finish

