



1.1

1.2

1.3

1.4

1 d ₁	2 d ₂	3 Length l					d ₄	h ₁ ≈	h ₂ ≈
32	M 6	16	20	30	-	-	12	21	10
40	M 8	20	30	40	50	-	14	24	12
50	M 10	20	30	40	50	60	18	30	16,5
60	M 12	20	30	40	50	60	20	37,5	20

2.1

Specification

- **GN 5334**
Stainless steel AISI 304
 - **GN 5334.4**
Stainless steel AISI 316L
- This information applies to both standards:
- Knob drawn from stainless steel sheet
 - Hub with threaded stud welded
 - Matte shot-blasted
 - *Stainless Steel Characteristics* → Page 2166
 - RoHS

Information

The original ELESA design with 5 recess grips is typical for star knobs with threaded stud GN 5334 / GN 5334.4.

This form gives these grips an appealing look and additionally allows a high torque to be achieved.

Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

- *Wing Screws GN 835 (Stainless Steel)* → Page 619
- *Star Knobs with Threaded Stud GN 6336.5 (Stainless Steel)* → Page 541
- *Hand Knobs with Threaded Stud GN 6335.5 (Stainless Steel)* → Page 583
- *Star Knobs with Threaded Stud GN 5334 (Stainless Steel, with Loss Protection GN 111.7)* → Page 2084

2.2

2.3

2.4

How to order (Stainless steel AISI 304)

GN 5334-50-M10-40

1 d ₁
2 d ₂
3 Length l

How to order (Stainless steel AISI 316L)

GN 5334.4-60-M12-30

1 d ₁
2 d ₂
3 Length l

