

elesa
Original design DD50 / DD50.SST




2 Display position

- AN** On the chamfer, above
- AR** On the chamfer, below
- FN** In the front, above
- FR** In the front, below

3 Counting direction

- R** Digits ascending clockwise
- L** Digits ascending anti-clockwise

Display position



Counting direction







1

Counter

Indication after one spindle revolution

000	000	000	Corresponds to thread pitch	Max. revolutions per minute
003	00.3	0.03	0,3	1500
010	01.0	0.10	1	1500
020	02.0	0.20	2	1250
030	03.0	0.30	3	830
040	04.0	0.40	4	625
050	05.0	0.50	5	500
100	10.0	1.00	10	250

Mounting instructions and accessories	
<p>When mounting the position indicator, an appropriately situated mounting hole is required for the torque support.</p> 	<p>If the position indicator is used with smaller shaft diameters, the hollow shaft diameter Ø 10 H7 can be reduced with adapter bushings GN 952.1 (→ Page XYZ).</p> 
<p>Clamping plates GN 955.6 (→ Page XYZ) can be used to clamp spindles after adjustment to secure them against independent or accidental turning.</p> 	<p>If reduction is desired in addition to installation of a control knob, control knobs GN 957 (→ Page XYZ) are available, which combine both functions in a single element.</p> 

Specification	
Housing	
Plastic, polyamide (PA)	
• Color	<div> <div>OR</div> <div>GR</div> <div>SG</div> </div> <ul style="list-style-type: none"> - Orange, RAL 2004, shiny finish - Gray, RAL 7035, shiny finish - Black-gray, RAL 7021, shiny finish
• Operating temperature 0 °C to +80 °C	
• Oil and solvent resistant	
Sight glass	
Plastic, polyamide (PA-T), transparent	
Counter	
• Digits white	
• Pre-decimal positions highlighted black	
• Decimal positions highlighted red with additional scale	
GN 955	
• Hollow shaft	
Steel, blackened	
Sealed with an O-ring	
• Grub screw DIN 916	
Steel, blackened	
GN 955.2	
• Hollow shaft	
Stainless steel AISI 303	
Sealed with an O-ring	
• Grub screw DIN 916	
Stainless steel	

RoHS

Position indicators GN 955 / GN 955.2 have a directly driven counter with digital position indication. The digits are easy to read and appear enlarged due to the magnifying effect of the viewing window.

Both housing sections are ultrasonically welded, making the housing particularly stable and compact. The foam rubber seal prevents the transmission of vibration to the counter and serves as a seal.

Technical Information	Page
Further information for position indicators	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX
Accessory	
GN 952.1 Adapter Bushings	QVX
GN 955.6 Clamping Plates	QVX
GN 957 Control Knobs	QVX
GN 957.1 Control Knobs	QVX

How to order (Hollow shaft steel)	
<div> <div>1</div> <div>2</div> <div>3</div> <div>4</div> </div> GN 955-02.0-AR-R-OR	<div> <div>1</div> Counter </div> <div> <div>2</div> Display position </div> <div> <div>3</div> Counting direction </div> <div> <div>4</div> Color </div>
How to order (Hollow shaft stainless steel)	
<div> <div>1</div> <div>2</div> <div>3</div> <div>4</div> </div> GN 955.2-1.00-AN-L-SG	<div> <div>1</div> Counter </div> <div> <div>2</div> Display position </div> <div> <div>3</div> Counting direction </div> <div> <div>4</div> Color </div>