



<div>1</div> <div>d₁</div>	<div>2</div> <div>d₂</div>	d ₃	h ₁	h ₂	t min.
40	M 8	16	27	13,5	13
50	M 10	19	30	15	17

Specification

3

- Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black-gray, RAL 7021, matte finish  **SGA**
 - White, RAL 9016, matte finish  **WSA**
- Threaded bushing
Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Three-lobed knobs GN 5342 are manufactured from an antimicrobial plastic.

Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antimicrobial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

- *Product Family Sanline* → Page 2154
- *Star Knobs GN 5337.4 (Technopolymer, Bushing Stainless Steel)*
→ Page 564
- *Star Knobs GN 5337.4 with Loss Protection GN 111.7* → Page 2084

How to order	1 d ₁
<div>123</div> GN 5342-40-M8-WSA	2 d ₂
	3 Finish