



elesa
Original design BSA-T50



b	d ₁	d ₂	l ₁	l ₂	l ₃	l ₄	m ₁	m ₂
24	B 6	3,2	38	28	8	29,5	15	18

Specification

Clamping plate

- Plastic, Polyamide (PA-HP)
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Adjustable hand lever

- Handle
 - Plastic, Polyamide (PA)
 - Glass fiber reinforced
 - Operating temperature -30 °C to +130 °C
 - Black-gray, matte finish, similar RAL 7021
- Releasing button
 - Plastic, Polyamide (PA)
 - Black-gray, RAL 7021, shiny finish
- Bushing
 - Stainless steel AISI 304
- Hex head screw
 - Stainless steel AISI 316

Clamping plates GN 955.6 are used in connection with position indicators GN 955 / GN 955.2. The mounting holes support typical bore hole patterns. In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked. At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator. The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...	Page
GN 955 Position Indicators (Hollow Shaft Steel)	QVX
GN 955.2 Position Indicators (Hollow Shaft Stainless Steel)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

RoHS

How to order	1 b
GN955.6-24-B6	2 d ₁