



Length l	d ₁ H7 Bore	s H9 Square	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆ ≈	Ø Handle
100	B 12	V 12	24	23,5	30	33	52,5	10	17	16	65	22
125	B 14	V 14	28	26,5	35	40	62	14	18	18,5	80	24

Specification

Body Plastic, Polyamide (PA) <ul style="list-style-type: none">• Glass fiber reinforced• Operating temperature 0 °C to +90 °C• Black-gray, matte finish, similar to RAL 7021	Cover cap Plastic, Polyamide (PA) <ul style="list-style-type: none">• Black-gray, RAL 7021, matte finish• Orange, RAL 2004, matte finish• Gray, RAL 7035, matte finish• Yellow, RAL 1021, matte finish• Blue, RAL 5024, matte finish• Red, RAL 3000, matte finish	<ul style="list-style-type: none">● DSG● DOR● DGR● DGB● DBL● DRT
--	--	---

Hub bushing Steel, blackened
--

Threaded bushing to accept the revolving handle Brass
--

Revolving handle Plastic, Polyamide (PA) <ul style="list-style-type: none">• Black, matte finish• Spindle steel• Zinc plated, blue passivated

RoHS

The design of the cranked handles GN 670 matches the product family Ergostyle®.

The protruding steel bushing ensures an accurate bore and square to bore face. It can be retained with a pin or a retaining screw. The link between the cranked handle and shaft can be established either with a keyway or a follower pin.

Technical Information	Page
Product Family Ergostyle®	QVX
Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

Accessory	
GN 184 Countersunk Washers (for Axial Fixing)	QVX

How to order	
1 Length l	
2 d ₁ (s)	
3 Color of the cover cap	