




1 2 d	b ₁	b ₂	h ₁	h ₂	h ₃	Length l	r ₁	r ₂	s Stroke cam	r ₂ -h ₃ Total stroke
8	13	9	19,54	14	12	114	17,2	21,07	3,87	9,07
10	17	12	24,54	17	15	138	21,6	26,45	4,85	11,45
12	20	14	31,81	21	18	157	28	34,29	6,29	16,29

Specification

- GN 917**
Steel
 - ST 52-3 / German Material No. 1.0570
 - Blackened
- GN 917.1**
Stainless steel AISI 304
Shot-blasted

This information applies to both standards:

- King pin
Stainless steel AISI 420
Tempered
- Safety circlip DIN 471
Stainless steel AISI 301
- Plastic cap
 - Red, oil resistant
 - Temperature resistant up to 60 °C
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Double cam levers GN 917 / GN 917.1 are used for repositioning and clamping.

The eccentric cam has the advantage that the clamping force remains constant in every position of its travel and in addition is self arresting.

The dimension b₂ is made to match the head size of swing bolts DIN 444 and swing nuts GN 444.2 respectively.

see also...

- Swing Bolts DIN 444 → Page 1046
- Swing Nuts GN 444.2 → Page 1079
- Eccentric Cams GN 918 → Page 668

How to order (Steel) 12	1	d
	2	b ₁
GN917-10-17		
How to order (Stainless steel) 12	1	d
	2	b ₁
GN917.1-12-20		